



WMSS81N

1 Gang Double Pole Switched Socket with LED Indicator

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 13 A

Dimensions

Depth 25.8 mm

Height 86 mm

Width 86 mm

Cover, door

Cover Full cover plate

Materials

Colour white

Material Urea-formaldehyde

Surface appearance glossy

Type of surface treatment untreated

Connection

Type of connection screw

Cable

Wiring with earth connection

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Safety

Protection index IP IP20

Protection Enhanced contact protection