



WMSS81R

## 1 Gang Double Pole Switched Socket with Red Rocker

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	13 A

#### Dimensions

Depth	25.8 mm
Height	86 mm
Width	86 mm

#### Cover, door

Cover	Full cover plate
-------	------------------

#### Materials

Colour	white
Material	duroplastic
Type of surface treatment	untreated

#### Cable

Wiring	with earth connection
--------	-----------------------

#### Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

#### Safety

Protection index IP	IP20
Protection	Enhanced contact protection