



WMSS82-USBAC

Double Pole Switched Socket 2 GangComplete With Twin USB A+C Ports

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Rated voltage	220...240 V AC
---------------	----------------

Dimensions

Depth	19 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	white
Type of surface treatment	untreated

Cable

Wiring	with double earth connection
--------	------------------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

Safety

Protection index IP	IP20
Protection	Enhanced contact protection