



WMSS82R

2 Gang Double Pole Switched Socket Dual Earth Red Rockers

Technical characteristics

Electric current

Rated current	13 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Dimensions

Height	86 mm
Width	146 mm
Depth	29.50 mm

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	0
-------------------	---

Texts

Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	Enhanced contact protection