



WMSS82RR

IP20

2 Gang Double Pole Switched Socket Dual Earth red Face Plate & Rockers

Technical Characteristics

Fixing mode	flush-mounting
Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	13 A
Rated current	13 A
Depth	29.5 mm
Height	86 mm
Width	146 mm
Number of modules	0
Cover	Full cover plate
Colour	white
Material	Urea-formaldehyde
Surface appearance	glossy
Type of surface treatment	untreated
Colour syntax: Colour	white
Imprint	without imprint
Type of connection	screw
Wiring	with double earth connection
Component	with 2 fixing screws M3.5 x 30 mm
Protection index IP	IP20
Protection	Enhanced contact protection
Designation syntax: Core designation/function	socket outlet