



WMSS82USBS

## 2 Gang Double Pole Switched Socket Complete With Twin USB Ports and Spacer

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC

#### Dimensions

Depth	39.1 mm
Height	86 mm
Width	146 mm

#### Cover, door

Cover	Full cover plate
-------	------------------

#### Materials

Colour	white
Type of surface treatment	untreated

#### Cable

Wiring	with double earth connection
--------	------------------------------

#### Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

#### Safety

Protection index IP	IP20
Protection	Enhanced contact protection