



WMSS82/HOUSERNG

## 2 Gang Double Pole Switched Socket Dual Earth Marked HOUSERING

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Main electrical features

Nominal voltage	250 V
-----------------	-------

Rated voltage	220...230 V AC
---------------	----------------

Rated current	13 A
---------------	------

#### Dimensions

Depth	29.5 mm
-------	---------

Height	86 mm
--------	-------

Width	146 mm
-------	--------

#### Cover, door

Cover	Full cover plate
-------	------------------

#### Materials

Colour	white
--------	-------

Type of surface treatment	untreated
---------------------------	-----------

#### Connection

Type of connection	screw
--------------------	-------

#### Safety

Protection index IP	IP20
---------------------	------

Protection	Enhanced contact protection
------------	-----------------------------