



WMSSU83/DW



13A FCU Switched Marked DISHWASHER

Technical characteristics

Electric current

| | |
|---------------|------|
| Rated current | 13 A |
|---------------|------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|----------------|-------------------|
| Colour | White |
| Surface finish | Glossy |
| Material | Urea formaldehyde |
| Treatment | Untreated |

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Dimensions

| | |
|----------------|----------|
| Built-in depth | 25.30 mm |
|----------------|----------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Texts

| | |
|-------------------|--|
| Installation mode | For flush-mounted and hollow wall mounting |
| Lighting | Without lighting (cannot be illuminated) |
| Switch mode | 2-pole |