



WPPS32BW

**10AX 3 Gang 2 Way Wall Switch & Back Box without Knockouts White**

**Technical Characteristics**

Switch mode	2 way
Frequency	50/60 Hz
Rated current	10 AX
Depth	24 mm
Height	86 mm
Width	86 mm
Colour	white
Material	Steel
Imprint	with clear terminal markings
Terminal	unique patented loop terminal allows neutral looping at the switch
Component	with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each
Lighting	without lighting (cannot be illuminated)
Standard	BS EN 60669-1