



WPSS81

1 Gang Double Pole Switched Socket

Technical characteristics

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	13 A

Dimensions

Depth	25.8 mm
Height	86 mm
Width	86 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Type of surface treatment	Epoxy
---------------------------	-------

Cable

Wiring	with earth connection
--------	-----------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each
-----------	---

Safety

Protection index IP	IP20
Protection	Enhanced contact protection