



WPSS81B

1 Gang Double Pole Switched Socket & Back Box without Knockouts

Technical characteristics

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	13 A

Dimensions

Depth	53.2 mm
Height	86 mm
Width	86 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	grey
Material	Steel

Connection

Type of connection	screw
--------------------	-------

Safety

Protection index IP	IP20
Protection	Enhanced contact protection