



WPSS81BKO

### 1 Gang Double Pole Switched Socket & Back Box with Knockouts

#### Technical characteristics

##### Architecture

Fixing mode	surface-mounting
-------------	------------------

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	13 A

##### Dimensions

Depth	53.2 mm
Height	86 mm
Width	86 mm

##### Connection

Type of connection	screw
--------------------	-------

##### Safety

Protection index IP	IP20
---------------------	------