



WPSS81N

### 1 Gang Double Pole Switched Socket with LED Indicator

#### Technical characteristics

##### Architecture

Fixing mode	surface-mounting
-------------	------------------

##### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	13 A

##### Dimensions

Depth	26 mm
Height	86 mm
Width	86 mm

##### Cover, door

Cover	Full cover plate
-------	------------------

##### Materials

Colour	grey
Material	Steel

##### Connection

Type of connection	screw
--------------------	-------

##### Safety

Protection index IP	IP20
Protection	Enhanced contact protection