



WPSS81NBKOW



1 Gang Double Pole Switched Socket with LED Indicator & Back Box with KOs White

Technical Characteristics

Fixing mode	surface-mounting
Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	13 A
Rated current	13 A
Depth	53.2 mm
Height	86 mm
Width	86 mm
Number of modules	0
Cover	Full cover plate
Colour	white
Material	Steel
Surface appearance	glossy
Type of surface treatment	Epoxy
Colour syntax: Colour	white
Imprint	without imprint
Type of connection	screw
Wiring	with earth connection
Component	with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each
Protection index IP	IP20
Protection	Enhanced contact protection
Designation syntax: Core designation/function	socket outlet