



WPSS81NBW

### 1 Gang Double Pole Switched Socket with LED Indicator & Back Box wo KOs White

#### Technical characteristics

##### Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	13 A

##### Dimensions

Depth	53.2 mm
Height	86 mm
Width	86 mm

##### Cover, door

Cover	Full cover plate
-------	------------------

##### Materials

Colour	white
Type of surface treatment	Epoxy

##### Cable

Wiring	with earth connection
--------	-----------------------

##### Scope of delivery

Component	with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each
-----------	---

##### Safety

Protection index IP	IP20
Protection	Enhanced contact protection