



WPSS82-USB

13A 2 Gang Double Pole Switched Socket c/w Twin USB Ports shallow

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	220...240 V AC

Dimensions

Depth	53.2 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Type of surface treatment	Epoxy
---------------------------	-------

Cable

Wiring	with double earth connection
--------	------------------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each
-----------	---

Safety

Protection index IP	IP20
Protection	Enhanced contact protection