



WPSS82

## 2 Gang Double Pole Switched Socket

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	13 A

#### Dimensions

Depth	53.2 mm
Height	86 mm
Width	146 mm

#### Connection

Type of connection	screw
--------------------	-------

#### Safety

Protection index IP	IP20
---------------------	------