



WPSS82B-USB

13A 2 Gang Double Pole Switched Socket c/w Twin USB & Back Box without Knockouts

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	220...240 V AC

Dimensions

Depth	53.2 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Colour	grey
Material	Steel

Connection

Type of connection	screw
--------------------	-------

Safety

Protection index IP	IP20
Protection	Enhanced contact protection