



WPSS82B

2 Gang Double Pole Switched Socket & Back Box without Knockouts

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	13 A

Dimensions

Depth	53.2 mm
Height	86 mm
Width	146 mm

Connection

Type of connection	screw
--------------------	-------

Safety

Protection index IP	IP20
---------------------	------