



WPSS82NBKO

**IP20**

**2 Gang Double Pole Switched Socket with LED Indicator & Back Box with Knockouts**

**Technical Characteristics**

|   |   |
|---|---|
| Fixing mode                                   | flush-mounting  |
| Nominal voltage                               | 250 V   |
| Rated voltage                                 | 220...230 V AC  |
| Rated current                                 | 13 A  |
| Rated current                                 | 13 A  |
| Depth   | 53.2 mm   |
| Height  | 86 mm   |
| Width   | 146 mm  |
| Number of modules                             | 0   |
| Cover   | Full cover plate  |
| Colour  | grey  |
| Material                                      | Steel   |
| Surface appearance                            | glossy  |
| Type of surface treatment                     | Epoxy   |
| Colour syntax: Colour                         | grey  |
| Imprint                                       | without imprint   |
| Type of connection                            | screw   |
| Wiring  | with double earth connection                            |
| Component                                     | with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each |
| Protection index IP                           | IP20  |
| Protection                                    | Enhanced contact protection                             |
| Designation syntax: Core designation/function | socket outlet   |