



WPSS82NW

## 2 Gang Double Pole Switched Socket with LED Indicator White

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
-------------	----------------

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Rated current	13 A

#### Dimensions

Depth	53.2 mm
Height	86 mm
Width	146 mm

#### Cover, door

Cover	Full cover plate
-------	------------------

#### Materials

Colour	white
Type of surface treatment	Epoxy

#### Cable

Wiring	with double earth connection
--------	------------------------------

#### Scope of delivery

Component	with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each
-----------	---

#### Safety

Protection index IP	IP20
Protection	Enhanced contact protection