



WPSS82OBKOW

## 2 Gang Double Pole Switched Socket Outboard Rockers & Back Box with KOs White

### Technical characteristics

#### Architecture

|             |                |
|-------------|----------------|
| Fixing mode | flush-mounting |
|-------------|----------------|

#### Main electrical features

|                 |                |
|-----------------|----------------|
| Nominal voltage | 250 V          |
| Rated voltage   | 220...230 V AC |
| Rated current   | 13 A           |

#### Dimensions

|        |         |
|--------|---------|
| Depth  | 53.2 mm |
| Height | 86 mm   |
| Width  | 146 mm  |

#### Cover, door

|       |                  |
|-------|------------------|
| Cover | Full cover plate |
|-------|------------------|

#### Materials

|                           |       |
|---------------------------|-------|
| Colour                    | white |
| Type of surface treatment | Epoxy |

#### Cable

|        |                              |
|--------|------------------------------|
| Wiring | with double earth connection |
|--------|------------------------------|

#### Scope of delivery

|           |   |
|-----------|---|
| Component | with 2 fixing screws M3.5 x 20 mm and M3.5 x 30 mm each |
|-----------|---|

#### Safety

|                     |                             |
|---------------------|-----------------------------|
| Protection index IP | IP20                        |
| Protection          | Enhanced contact protection |