



WRCC50BNB

Technical characteristics

Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	45 A

Dimensions

Depth	39.6 mm
Height	86 mm
Width	146 mm

Cover, door

Cover	Full cover plate
-------	------------------

Materials

Surface appearance	matt
--------------------	------

Cable

Wiring	with double earth connection
--------	------------------------------

Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

Safety

Protection	to protect downstream loads
------------	-----------------------------

Use conditions

Insert	insert, black
--------	---------------