



WRCC50NBNB

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Nominal voltage 250 V

Rated voltage 220...230 V AC

Rated current 45 A

Dimensions

Depth 39.6 mm

Height 86 mm

Width 146 mm

Cover, door

Cover Full cover plate

Materials

Colour black

Material stainless steel

Surface appearance matt

Type of surface treatment Nickel-plated

Connection

Type of connection Screw connection

Safety

Protection index IP IP20

Protection to protect downstream loads

Use conditions

Insert insert, black