



WRCC50NBSW



## 45A Cooker Control Unit Brushed Steel White Insert

### Technical characteristics

#### Electric current

Rated current	45 A
---------------	------

#### Voltage

Rated voltage	250 V
Nominal voltage	250 - 250 V

#### Materials

Colour	Stainless steel
Surface finish	Matt
Material	Stainless steel
Treatment	Brushed

#### Dimensions

Height	86 mm
Width	146 mm
Depth	39.60 mm

#### Connection

Conductor cross-section	16 - 16 mm <sup>2</sup>
-------------------------	-------------------------

#### Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

#### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

#### Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	Yes

#### Accessories

Has labelling field	No
---------------------	----

#### Capacity

Number of modules	0
-------------------	---

<b>Safety</b>	
Ingress Protection (IP) class	IP20
<b>Functions</b>	
With orientation lighting	No
With function lighting	Yes
<b>Texts</b>	
Imprint	Without imprint
Cover	Full cover plate
Wiring	With double earth connection
Protection	To protect downstream loads