



WRCC50NBSW

## 45A Cooker Control Unit Brushed Steel White Insert

### Technical characteristics

#### Main electrical features

|                 |          |
|-----------------|----------|
| Nominal voltage | 250 V    |
| Rated voltage   | 250 V AC |
| Rated current   | 45 A     |

#### Dimensions

|        |         |
|--------|---------|
| Depth  | 39.6 mm |
| Height | 86 mm   |
| Width  | 146 mm  |

#### Cover, door

|       |                  |
|-------|------------------|
| Cover | Full cover plate |
|-------|------------------|

#### Materials

|                    |      |
|--------------------|------|
| Surface appearance | matt |
|--------------------|------|

#### Connection

|                    |                  |
|--------------------|------------------|
| Type of connection | Screw connection |
|--------------------|------------------|

#### Cable

|        |                              |
|--------|------------------------------|
| Wiring | with double earth connection |
|--------|------------------------------|

#### Scope of delivery

|           |                                   |
|-----------|-----------------------------------|
| Component | with 2 fixing screws M3.5 x 30 mm |
|-----------|-----------------------------------|

#### Safety

|            |                             |
|------------|-----------------------------|
| Protection | to protect downstream loads |
|------------|-----------------------------|

#### Use conditions

|        |              |
|--------|--------------|
| Insert | insert white |
|--------|--------------|