



WRCC50NPBB

## Technical characteristics

### Architecture

Fixing mode	flush-mounting
-------------	----------------

### Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	45 A

### Dimensions

Depth	39.6 mm
Height	86 mm
Width	146 mm

### Cover, door

Cover	Full cover plate
-------	------------------

### Materials

Type of surface treatment	Anodised
---------------------------	----------

### Cable

Wiring	with double earth connection
--------	------------------------------

### Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

### Safety

Protection index IP	IP20
Protection	to protect downstream loads

### Use conditions

Insert	insert, black
--------	---------------