



WRCC50NPBB

## Technical characteristics

### Architecture

Fixing mode flush-mounting

### Main electrical features

Nominal voltage 250 V

Rated voltage 220...230 V AC

Rated current 45 A

### Dimensions

Depth 39.6 mm

Height 86 mm

Width 146 mm

### Materials

Material stainless steel

Type of surface treatment Anodised

### Connection

Type of connection Screw connection

### Safety

Protection index IP IP20

Protection to protect downstream loads

### Use conditions

Insert insert, black