



WRCC50NPBB

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Nominal voltage 250 V

Rated voltage 220...230 V AC

Rated current 45 A

Dimensions

Depth 39.6 mm

Height 86 mm

Width 146 mm

Materials

Material stainless steel

Type of surface treatment Anodised

Connection

Type of connection Screw connection

Safety

Protection index IP IP20

Protection to protect downstream loads

Use conditions

Insert insert, black