



WRCC50NPSW

45A Cooker Control Unit Polished Steel White Insert

Technical characteristics

Architecture

Fixing mode flush-mounting

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Rated current 45 A

Dimensions

Depth 39.6 mm

Height 86 mm

Width 146 mm

Cover, door

Cover Full cover plate

Materials

Colour silver optics

Material stainless steel

Surface appearance glossy

Type of surface treatment Other

Connection

Type of connection Screw connection

Cable

Wiring with double earth connection

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Safety

Protection index IP IP20

Protection to protect downstream loads

Use conditions

Insert insert white