



WRDP50NBSB



### 50A Double Pole Switch 1 Gang with LED Indicator Brushed Steel Black Insert

#### Technical characteristics

##### Electric current

Rated current	50 A
---------------	------

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Materials

Colour	Stainless steel
Surface finish	Mat
Material	Stainless steel
Treatment	Brushed

##### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	1
-------------------	---

##### Dimensions

Built-in depth	20.20 mm
----------------	----------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Architecture

Control/operation element	Single rocker
---------------------------	---------------

##### Texts

Lighting	With control LED for ON
Switch mode	2-pole