



WRDP50NPSW



50A Double Pole Switch 1 Gang with LED Indicator Polished Steel White Insert

Technical characteristics

Electric current

Rated current 50 A

Installation, mounting

Mounting on Flush mounting

Voltage

Rated voltage 250 V

Materials

Colour Silver

Surface finish Glossy

Material Stainless steel

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 1

Dimensions

Built-in depth 20.20 mm

Safety

Ingress Protection (IP) class IP20

Architecture

Control/operation element Single rocker

Texts

Lighting With control LED for ON

Switch mode 2-pole