



WRDP84FOBSW



## 20A Double Pole Switch with Flex Outlet Brushed Steel White Insert

### Technical characteristics

#### Electric current

|               |      |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

#### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

#### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

#### Materials

|                |                 |
|----------------|-----------------|
| Colour         | Stainless steel |
| Surface finish | Mat             |
| Material       | Stainless steel |
| Treatment      | Brushed         |

#### Identification

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

#### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

#### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

#### Dimensions

|                |       |
|----------------|-------|
| Built-in depth | 20 mm |
|----------------|-------|

#### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

#### Architecture

|                           |               |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

#### Texts

|             |  |
|-------------|--|
| Lighting    | Without lighting (cannot be illuminated) |
| Switch mode | 2-pole                                   |