



WRDP84FOPSB



20A Double Pole Switch with Flex Outlet Polished Steel Black Insert

Technical characteristics

Electric current

| | |
|---------------|------|
| Rated current | 20 A |
|---------------|------|

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|----------------|-----------------|
| Colour | Silver |
| Surface finish | Glossy |
| Material | Stainless steel |

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Dimensions

| | |
|----------------|-------|
| Built-in depth | 20 mm |
|----------------|-------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Single rocker |
|---------------------------|---------------|

Texts

| | |
|-------------|--|
| Lighting | Without lighting (cannot be illuminated) |
| Switch mode | 2-pole |