



WRDP84FOPSW



20A Double Pole Switch with Flex Outlet Polished Steel White Insert

Technical characteristics

Electric current

Rated current	20 A
---------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Silver
Surface finish	Glossy
Material	Stainless steel

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Built-in depth	20 mm
----------------	-------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Texts

Lighting	Without lighting (cannot be illuminated)
Switch mode	2-pole