



WRDP84NIBSW



## 20A Double Pole Switch Isolation Function with LED Brushed Steel White Insert

### Technical characteristics

#### Electric current

Rated current	20 A
---------------	------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Materials

Surface finish	Glossy, Mat
Material	Stainless steel
Treatment	Untreated

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	1
-------------------	---

#### Dimensions

Built-in depth	21.90 mm
Built-in depth flush-mounted boxes	25 mm

#### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

#### Architecture

Control/operation element	Single rocker
---------------------------	---------------

#### Texts

Lighting	With control LED for ON
Switch mode	2-pole