



WRDS4BS

#### 4 Gang Dimmer Switch 250W Brushed Steel

##### Technical characteristics

##### Main electrical features

Frequency 50/60 Hz

##### Voltage

Operating voltage 240 V AC

##### Connection

Type of load inductive

##### Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

##### Equipment

Dimming principle phase cut-on