



WRPS12BNB

#### Technical characteristics

##### Configuration

Switch mode 2 way

##### Main electrical features

Frequency 50/60 Hz

Rated current 10 AX

##### Dimensions

Depth 24 mm

Height 86 mm

Width 86 mm

##### Connection

Terminal unique patented loop terminal allows neutral looping at the switch

##### Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

##### Equipment

Lighting without lighting (cannot be illuminated)

##### Standards

Standard BS EN 60669-1

##### Use conditions

Insert insert, black