



WRPS16BNB

Technical characteristics

Configuration

Switch mode intermediate

Main electrical features

Frequency 50/60 Hz

Rated current 20 A

Dimensions

Depth 24 mm

Height 86 mm

Width 86 mm

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Equipment

Lighting without lighting (cannot be illuminated)

Use conditions

Insert insert, black