



WRPS16BNB

#### Technical characteristics

##### Configuration

Switch mode intermediate

##### Main electrical features

Frequency 50/60 Hz

Rated current 20 A

##### Dimensions

Depth 24 mm

Height 86 mm

Width 86 mm

##### Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

##### Equipment

Lighting without lighting (cannot be illuminated)

##### Use conditions

Insert insert, black