



WRPS22BNB

Technical characteristics

Configuration

Switch mode 2 way

Main electrical features

Frequency 50/60 Hz

Rated current 10 AX

Dimensions

Depth 24 mm

Height 86 mm

Width 86 mm

Connection

Terminal unique patented loop terminal allows neutral looping at the switch

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Equipment

Lighting without lighting (cannot be illuminated)

Standards

Standard BS EN 60669-1

Use conditions

Insert insert, black