



WRPS32BNB

### Technical characteristics

#### Configuration

Switch mode 2 way

#### Main electrical features

Frequency 50/60 Hz

Rated current 10 AX

#### Dimensions

Depth 24 mm

Height 86 mm

Width 86 mm

#### Connection

Terminal unique patented loop terminal allows neutral looping at the switch

#### Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

#### Equipment

Lighting without lighting (cannot be illuminated)

#### Standards

Standard BS EN 60669-1

#### Use conditions

Insert insert, black