



WRPS32BSW



10AX 3 Gang 2 Way Wall Switch Brushed Steel White Insert

Technical characteristics

Electric current

| | |
|-------------------|------|
| Switching current | 10 A |
| Rated current | 10 A |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Materials

| | |
|----------------|-----------------|
| Colour | Stainless steel |
| Surface finish | Mat |
| Material | Stainless steel |
| Treatment | Brushed |

Identification

| | |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

| | |
|-------------------|---|
| Number of buttons | 3 |
|-------------------|---|

Dimensions

| | |
|----------------|----------|
| Built-in depth | 11.20 mm |
|----------------|----------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Architecture

| | |
|---------------------------|---------------|
| Control/operation element | Triple rocker |
|---------------------------|---------------|

Texts

| | |
|-------------------|--|
| Installation mode | For flush-mounted and hollow wall mounting |
| Lighting | Without lighting (cannot be illuminated) |
| Switch mode | 2-way |