



WRPS42PSW



### 10AX 4 Gang 2 Way Wall Switch Polished Steel White Insert

#### Technical characteristics

##### Electric current

Switching current	10 A
Rated current	10 A

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Materials

Colour	Silver
Surface finish	Glossy
Material	Stainless steel

##### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

##### Connectivity

Mounting type	Screw mounting
---------------	----------------

##### Controls and indicators

Number of buttons	4
-------------------	---

##### Dimensions

Built-in depth	11.20 mm
----------------	----------

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Architecture

Control/operation element	4-gang rocker
---------------------------	---------------

##### Texts

Installation mode	For flush-mounted and hollow wall mounting
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way