



WRS51BNB

#### Technical characteristics

##### Architecture

Fixing mode	flush-mounting
-------------	----------------

##### Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	5 A

##### Dimensions

Depth	25 mm
Height	86 mm
Width	86 mm

##### Cover, door

Cover	Full cover plate
-------	------------------

##### Materials

Surface appearance	matt
Type of surface treatment	Nickel-plated

##### Cable

Wiring	with earth connection
--------	-----------------------

##### Scope of delivery

Component	with 2 fixing screws M3.5 x 30 mm
-----------	-----------------------------------

##### Safety

Protection index IP	IP20
Protection	Enhanced contact protection

##### Use conditions

Insert	insert, black
--------	---------------