



WRS51BSB



**IP20**



**5A 1 Gang Unswitched Socket Brushed Steel Black Insert**

**Technical Characteristics**

Fixing mode	flush-mounting
Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	5 A
Rated current	5 A
Depth	25 mm
Height	86 mm
Width	86 mm
Number of modules	0
Cover	Full cover plate
Colour	stainless steel optics
Material	stainless steel
Surface appearance	matt
Type of surface treatment	brushed
Colour syntax: Colour	stainless steel
Inprint	without imprint
Type of connection	screw
Wiring	with earth connection
Component	with 2 fixing screws M3.5 x 30 mm
Protection index IP	IP20
Protection	Enhanced contact protection
Insert	insert, black
Designation syntax: Core designation/function	socket outlet