



WRS51PBB

#### Technical characteristics

##### Architecture

Fixing mode	flush-mounting
-------------	----------------

##### Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	5 A

##### Dimensions

Depth	25 mm
Height	86 mm
Width	86 mm

##### Materials

Material	stainless steel
Type of surface treatment	Anodised

##### Connection

Type of connection	screw
--------------------	-------

##### Safety

Protection index IP	IP20
---------------------	------

##### Use conditions

Insert	insert, black
--------	---------------