



WRSO100BNB

Technical characteristics

Architecture

Number of poles 2pole

Main electrical features

Nominal voltage 250 V

Rated voltage 220...230 V AC

Rated current $\approx 87...174$ mA

Dimensions

Depth 54.5 mm

Height 146 mm

Width 86 mm

Cover, door

Cover Full cover plate

Materials

Surface appearance matt

Connection

Type of connection screw

Type of connection with screw terminals

Cable

Wiring with double earth connection

Scope of delivery

Component with 2 fixing screws M3.5 x 30 mm

Safety

Protection Enhanced contact protection

Use conditions

Insert insert, black