



WRSO100BSW

## 115/230V Shaver Outlet Brushed Steel White Insert

### Technical characteristics

#### Architecture

Fixing mode	flush-mounting
Number of poles	2pole

#### Main electrical features

Nominal voltage	250 V AC
Rated current	≈ 87...174 mA

#### Dimensions

Depth	54.5 mm
Height	146 mm
Width	86 mm

#### Materials

Colour	stainless steel optics
Material	stainless steel
Surface appearance	matt
Type of surface treatment	brushed

#### Connection

Type of connection	screw
Type of connection	with screw terminals

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Insert	insert white
--------	--------------