



WRSO100PBB

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole

Main electrical features

Nominal voltage	250 V
Rated voltage	220...230 V AC
Rated current	≈ 87...174 mA

Dimensions

Depth	54.5 mm
Height	146 mm
Width	86 mm

Materials

Material	stainless steel
Type of surface treatment	Anodised

Connection

Type of connection	screw
Type of connection	with screw terminals

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Insert	insert, black
--------	---------------